

UltraSeal® 3000 12x12

Sealed Edge Cleanroom Laundered 100% Polyester Knit wiper

UltraSeal[®] 3000 is a high sorbency, tubular, sealed edge cleanroom laundered two-ply wiper required for ISO Class 3 and above environments composed of 100% continuous filament polyester knit fabric. These properties provide UltraSeal[®] 3000 with the highest level of cleanliness, abrasion resistance and chemical compatibility required for ISO Class 3 and above environments and applications requiring critical control of contaminants combined with superior performance. UltraSeal[®] 3000 provides excellent cleaning effectiveness in tough applications due to patented edge seal and pinsonic design.



Other Class 3 and above wipers

- MicroSeal SuperSorb[®]
- MicroSeal SuperSorb[®] Lite
- MicroSeal[®]1 200
- MicroSeal[®]VP
- ValuSeal^{®-}LP
- ValuSeal^{®-}HA
- ValuSeal[®]1500

Key Attributes

- 100% continuous filament polyester knit
- Two-ply pinsonic tubular construction
- Patented sealed edge process for reduced fibre contamination; Patent #5,229,181
- Laundered and packaged in Berkshire's ISO Class 4 cleanroom

Benefits

- · Critically low particles, fibres, ions and extractables
- Chemically compatible with IPA and other solvents
- High sorbency level
- Pinsonic design adds surface texture that aids in stubborn residue removal
- Patented sealed edge process combined with tubular design offers excellent abrasion resistance for the toughest cleaning applications

Applications

- Designed for use in ISO Class 3 and higher cleanroom environments
- Designed for the highest level of contamination control in critical processing applications
- Excellent for spill control and processing areas where sorbency is of importance
- Chamber cleaning and CMP processing
- Designed for removal of tough residues in critical applications
- Steam autoclavable for aseptic applications
- Cleaning of medical device products
- Removing cleaning and disinfecting solution

Value Pack Option

The value pack option provides the same great performance in a more economical bulk packaging format.

Pre-Wetted Option

The same wiper material can be provided in pre-wetted formats for reduced VOC emissions, increased convenience, increased productivity, improved solvent control and cleaning protocol repeatability and reduced costs.

Sterile Validated Option

For aseptic processing areas, the same wiper material can be provided in a gamma irradiated validated sterile to a 10⁻⁶

www.berkshire.uk.com

Contact: Tel + 44 1953 562800 enquiries@berkshire.uk.com

America	Tel 1 413 528 2602	info@berkshire.com
Europe	Tel + 44 1953 562800	enquiries@berkshire.uk.com
SE Asia	Tel 65 6252 4313	enquiries@berkshire.com.sg
Japan	Tel 81 3 4530 9883	master@berkshire.co.jp

BC_3150_09-2023



Technical Data:

Attribute		Units	Value	Test Method	
Basis Weight		g/m ²	145	TAPPI T-410	
Caliper		μm	418	TAPPI T-411	
Fibres	≥100µm	fibres/cm ²	0.032	IEST-RP-CC004.4 Sec 7.1.3/Sec 7.2.2 modified	
Particles	<u>≥</u> 0.5µm	x10 ³ /cm ²	0.71	IEST-RP-CC004.4 Sec 7.1.3/Sec 7.2.1 modified	
Sorbency	Capacity	mL/m ²	418	IEST-RP-CC004.4 Sec 9.1 / Sec 9.2 modified	
	Efficiency	mL/g	2.9		
	Rate	seconds	1		
Non-Volatile Residue	DI Water	g/m ²	0.0039	IEST-RP-CC004.4 Sec 8.1.2	
	IPA	g/m ²	0.021		
Ions	Na ⁺	ppm	0.014	IEST-RP-CC004.4 Sec 8.2.2	
	K+	ppm	0.081		
	Ca++	ppm	0.012		
	Mg ⁺⁺	ppm	0.0037		
	CI-	ppm	0.044		


Notes:

.

- Technical data represented in this table are typical values at the time of publication. These should not be used as
 product specifications.
- Due to differences in test methods applied and equipment utilised by different wiper manufacturers, valid product
 comparisons may only be obtained through side-by-side testing in the same test facility, under similar conditions
 - Third party testing can be performed upon request

Order Information:

Product	Number	Size	Shts/pk	Pks/cs	Style
UltraSeal [®] 3000	US3000.1212.8	12x12" (30x30cm)	100	6	Stacked



www.berkshire.uk.com

Contact: Tel + 44 1953 562800 / info@berkshire.uk.com BC_3150_09-2023